

# HUBBELL Premise Wiring

## 20A Kitchen Counter Receptacle, Surface Mount, Bronze

By Hubbell Premise Wiring  
Catalog # [RCT220BZE](#)

20A Kitchen Counter Receptacle, Surface Mount, Bronze



### Features

- Spill water tested
- UL Listed for countertop installation.
- Permanent installation ready (suitable for MC cable or non-metallic sheath cable)
- Push down to pop-up function is rated for a minimum of 10,000 cycles
- Easy installations - simply drop in and tighten.

### Application

Power on Counter Top

### Specifications

Industry Standard(s)	UL
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-20R

### Conductor

Cable Entry	Kos in Bottom
Number Of Wires	3
Number Of Poles	2

### Configuration

Number Of Outlets	1 Duplex
-------------------	----------

### Current

Current / Amperage Rating	20 A
---------------------------	------

Voltage Rating Description	125 V
----------------------------	-------

### Dimensions

Size	Standard Sized
Width	4.20 in
Height	6.48 in
Length	4.20 in
Dimensions	4.20 in x 4.20 in x 6.48 in

### General

Construction Material - Main	220 Meunt
Sub Brand	Furniture Boxes
Construction	Fabricated
Type	Power Only
Series	Countertop Receptacle
Material	220 Meunt
UPC	883778309502
Style	Surface
Color	Bronze
Mounting Type	In Kitchen Counter Top

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)