

HUBBELL Premise Wiring

20A Kitchen Counter Receptacle, Flush Mount, Chrome

By Hubbell Premise Wiring
Catalog # [RCT221CH](#)

20A Kitchen Counter Receptacle, Flush Mount, Chrome



Features

- Spill water tested
- UL Listed for countertop installation.
- Permanent installation ready (suitable for MC cable or non-metallic sheath cable)
- Push down to pop-up function is rated for a minimum of 10,000 cycles
- Easy installations - simply drop in and tighten.

Application

Power on Counter Top

Specifications

Industry Standard(s)	UL
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-20R

Conductor

Cable Entry	Kos in Bottom
Number Of Wires	3
Number Of Poles	2

Configuration

Number Of Outlets	1 Duplex
-------------------	----------

Current

Current / Amperage Rating	20 A
---------------------------	------

Voltage Rating Description	125 V
----------------------------	-------

Dimensions

Size	Standard Sized
Width	4.20 in
Height	6.48 in
Length	4.20 in
Dimensions	4.20 in x 4.20 in x 6.48 in

General

Construction Material - Main	221 Meunt
Sub Brand	Furniture Boxes
Construction	Fabricated
Type	Power Only
Series	Countertop Receptacle
Material	221 Meunt
UPC	883778309588
Style	Flush
Color	Chrome
Mounting Type	In Kitchen Counter Top

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)