

LINKOSITY, Female Receptacle, 4-Pole, 10A, 10' Length

By Hubbell Wiring Device-Kellems
Catalog # [RF1004PA010](#)

LINKOSITY, Female Receptacle, 4-Pole, 10A, 10' Length



Oh No!
IMAGE COMING SOON

Features

- LINKOSITY4-Pole
- 10A
- 10' Length

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#16 AWG

Current

Current / Amperage Rating	10 A
Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585243160
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)