

Linkosity, Female Receptacle, 4-Wire, 10A, 5' Cable

By Hubbell Wiring Device-Kellems
Catalog # [RF1004PB005](#)

Linkosity, Female Receptacle, 4-Wire, 10A, 5' Cable



Oh No!
IMAGE COMING SOON

Features

- Linkosity4-Wire
- 10A
- 5' Cable

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#16 AWG

Current

Current / Amperage Rating	10 A
Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585128139
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)