

**HUBBELL**  
Wiring Device-Kellems

**Signal and Control, Linkosity, Female Receptacle, 4-Wire, 10A 600V AC, PM Wire Code, 5' Length**

By Hubbell Wiring Device-Kellems  
Catalog # [RF1004PM005](#)

Signal and Control, Linkosity, Female Receptacle, 4-Wire, 10A 600V AC, PM Wire Code, 5' Length

**Features**

- Linkosity4-Wire
- 10A 600V AC

**Application**

Power and Control Integration

**Specifications**

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

**Conductor**

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#16 AWG

**Current**

Current / Amperage Rating	10 A
---------------------------	------



**Oh No!**  
IMAGE COMING SOON

Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

**General**

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585131023
Color	Gray

**Logistics**

Carton Quantity	50
-----------------	----

**Product Assets**

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)