

10A, 5W, Female Receptacle, 1'

By Hubbell Wiring Device-Kellems
Catalog # [RF1005PE001](#)

10A, 5W, Female Receptacle, 1'



Features

- 10A
- 5W1'

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	5
Number Of Poles	5-Pole
Conductor Size	#16 AWG

Current

Current / Amperage Rating	10 A
---------------------------	------

Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585504476
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)