

## Linkosity, Female Receptacle, 10A, 10P, 10'

By Hubbell Wiring Device-Kellems  
Catalog # [RF1010PE010](#)

Linkosity, Female Receptacle, 10A, 10P, 10'



**Oh No!**  
IMAGE COMING SOON

### Features

- Linkosity10A
- 10P
- 10'

### Application

Power and Control Integration

### Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

### Conductor

Conductor Type	Copper
Number Of Conductors	10
Number Of Poles	10-Pole
Conductor Size	#16 AWG

### Current

Current / Amperage Rating	10 A
Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

### General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585505022
Color	Gray

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)