

Signal and Control, Linkosity, Female Receptacle, 2-Wire, 20A 600V AC, PE Wire Code, 1' Length

By Hubbell Wiring Device-Kellems
Catalog # [RF2002PE001](#)

Signal and Control, Linkosity, Female Receptacle, 2-Wire, 20A 600V AC, PE Wire Code, 1' Length



Features

- Linkosity2-Wire
- 20A 600V AC

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	2
Number Of Poles	2-Pole
Conductor Size	#12 AWG

Current

Current / Amperage Rating	20 A
---------------------------	------

Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585358284
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)