

## Linkosity, 20A 2W, Female Receptacle, 5'

By Hubbell Wiring Device-Kellems  
Catalog # [RF2002PE005](#)

Linkosity, 20A 2W, Female Receptacle, 5'



### Features

- Linkosity
- 20A 2W5'

### Application

Power and Control Integration

### Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

### Conductor

Conductor Type	Copper
Number Of Conductors	2
Number Of Poles	2-Pole
Conductor Size	#12 AWG

### Current

Current / Amperage Rating	20 A
---------------------------	------

Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

### General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585409634
Color	Gray

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)