

Linkosity, Female Receptacle, 20A 5W

By Hubbell Wiring Device-Kellems
Catalog # [RF2005PB010](#)

Linkosity, Female Receptacle, 20A 5W



Features

- Linkosity20A 5W

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	5
Number Of Poles	5-Pole
Conductor Size	#12 AWG

Current

Current / Amperage Rating	20 A
Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585409511
Color	Gray

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)