

## Signal and Control, Linkosity, Female Receptacle, 4-Wire, 20A 600V AC, PA Wire Code, 1' Length, Super, Neutral/IG

By Hubbell Wiring Device-Kellems  
Catalog # [RF2304PA001](#)

Signal and Control, Linkosity, Female Receptacle, 4-Wire, 20A 600V AC, PA Wire Code, 1' Length, Super, Neutral/IG



### Features

- Linkosity4-Wire
- 20A 600V AC

### Application

Power and Control Integration

### Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

### Conductor

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#12 AWG, #10 AWG Neutral

### Current

Current / Amperage Rating	20 A
---------------------------	------

Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

### General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585524696
Color	Gray

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)