

Linkosity, Female Receptacle, 20A Single,
4P, 5'

By Hubbell Wiring Device-Kellems
Catalog # [RF2304PA005](#)

Linkosity, Female Receptacle, 20A Single, 4P, 5'



Features

- Linkosity20A Single
- 4P
- 5'

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#12 AWG, #10 AWG Neutral

Current

Current / Amperage Rating	20 A
Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585524115
Color	Gray

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)