

Linkosity, Female Receptacle, 30A 4W, 5'

By Hubbell Wiring Device-Kellems
Catalog # [RF3004PB005](#)

Linkosity, Female Receptacle, 30A 4W, 5'



Features

- Linkosity30A 4W
- 5'

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#10 AWG

Current

Current / Amperage Rating	30 A
---------------------------	------

Current Rating	30 A
Amperage Rating	30 A
Wattage	18000
Voltage Rating	600V Max kV

General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585116471
Color	Gray

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)