

Linkosity, Female Receptacle, 4-Wire, 20A 600V AC, PA Wire Code, 5' Length, Super Neutral IG

By Hubbell Wiring Device-Kellems
Catalog # [RF3704PA005](#)

Linkosity, Female Receptacle, 4-Wire, 20A 600V AC, PA Wire Code, 5' Length, Super Neutral IG

Features

- Linkosity4-Wire
- 20A 600V AC
- PA Wire Code

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#10 AWG

Current



Current / Amperage Rating	30 A
Current Rating	30 A
Amperage Rating	30 A
Wattage	18000
Voltage Rating	600V Max kV

General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585358420
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)