

## Signal and Control, Linkosity, Female Receptacle, 20A 3W, Super Neutral, Isolated Ground

By Hubbell Wiring Device-Kellems  
Catalog # [RF7203PB005](#)

Signal and Control, Linkosity, Female Receptacle, 20A 3W, Super Neutral, Isolated Ground



### Features

- Linkosity20A 3W
- Super Neutral

### Application

Power and Control Integration

### Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

### Conductor

Conductor Type	Copper
Number Of Conductors	3
Number Of Poles	3-Pole
Conductor Size	#12 AWG, #10 AWG Neutral

### Current

Current / Amperage Rating	20 A
Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

### General

Item Type	Female Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585355665
Color	Gray

### Product Assets

[Catalog \[English\]](#)