

Incandescent Lamp Holders, Mogul Base, 5KV, 12" Wire Leads, Screw Mount

By Hubbell Wiring Device-Kellems
Catalog # [RL5221](#)

Incandescent Lamp Holders, Mogul Base, 5KV, 12" Wire Leads, Screw Mount



Features

- Mogul Base
- 5KV
- 12" Wire Leads
- Screw Mount

Application

HID Incandescent

Performance

Electrical - Rating - 1500W, 600V Max, 5KV Pulse, Mechanical - Terminal Accommodation - Wire leads: #14 AWG SF-2 (SEW-2) 200° C, 600V glass braid, 12 inch long, stripped 1/2 inch wire

Specifications

EU RoHS Indicator	No
Industry Standard(s)	C/US UL Listed

Current

Current Rating	2.5 A
Amperage Rating	2.5 A
Frequency Rating	60 Hz
Current / Amperage Rating	2.5 A
Connectivity	12" Leads
Voltage Rating	600V AC kV

Dimensions

Lamp Size

Mogul Base

General

Series	Lampholders
OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Replacement Incandescent Lampholders
Material - Mounting Hardware Type	Screw Mounting HID Incandescent, Porcelain Keyless
Material Specifications	Composite <ul style="list-style-type: none">• Lamp Type - EX39 socket• Material - Glazed porcelain body with ceramic arc shield Screw shell: Brass with nickel plate• Mounting - Screw mount, 12 inch leads
UPC	883778304057

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[French\]](#)