

Linkosity, 3A, 2W, Male Receptacle, 1'

By Hubbell Wiring Device-Kellems
Catalog # [RM0302PE001](#)

Linkosity, 3A, 2W, Male Receptacle, 1'



Features

- Linkosity
- 3A
- 2W
- Male Receptacle
- 1'

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	2
Number Of Poles	2-Pole
Conductor Size	#24 AWG

Current

Current / Amperage Rating	3 A
Current Rating	3 A
Amperage Rating	3 A
Wattage	1800
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585504223
Color	Gray

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)