

Linkosity, 3A, 3W, Male Receptacle, 5'

By Hubbell Wiring Device-Kellems
Catalog # [RM0303PE005](#)

Linkosity, 3A, 3W, Male Receptacle, 5'



Features

- Linkosity
- 3A
- 3W
- Male Receptacle
- 5'

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	3
Number Of Poles	3-Pole
Conductor Size	#24 AWG

Current

Current / Amperage Rating	3 A
Current Rating	3 A
Amperage Rating	3 A
Wattage	1800
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585116181
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)