

## Linkosity, 10A, 2W, Male Receptacle, 1'

By Hubbell Wiring Device-Kellems  
Catalog # [RM1002PE001](#)

Linkosity, 10A, 2W, Male Receptacle, 1'



### Features

- Linkosity
- 10A
- 2W
- Male Receptacle
- 1'

### Application

Power and Control Integration

### Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

### Conductor

Conductor Type	Copper
Number Of Conductors	2
Number Of Poles	2-Pole
Conductor Size	#16 AWG

### Current

Current / Amperage Rating	10 A
Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

### General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585504346
Color	Gray

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)