

Linkosity, Male Inlet, 10A, 3-Pole, 10' Length

By Hubbell Wiring Device-Kellems
Catalog # [RM1003PB010](#)

Linkosity, Male Inlet, 10A, 3-Pole, 10' Length



Features

- Linkosity10A
- 3-Pole
- 10' Length

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	3
Number Of Poles	3-Pole
Conductor Size	#16 AWG

Current

Current / Amperage Rating	10 A
Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585243184
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)