

Linkosity, Male Receptacle, 10A, 4P, 10'

By Hubbell Wiring Device-Kellems
Catalog # [RM1004PA010](#)

Linkosity, Male Receptacle, 10A, 4P, 10'



Features

- Linkosity10A
- 4P
- 10'

Application

Power and Control Integration

Specifications

| | |
|-------------------|----------|
| EU RoHS Indicator | Yes |
| Nema Rating | Non-NEMA |

Conductor

| | |
|----------------------|---------|
| Conductor Type | Copper |
| Number Of Conductors | 4 |
| Number Of Poles | 4-Pole |
| Conductor Size | #16 AWG |

Current

| | |
|---------------------------|-------------|
| Current / Amperage Rating | 10 A |
| Current Rating | 10 A |
| Amperage Rating | 10 A |
| Wattage | 6000 |
| Voltage Rating | 600V Max kV |

General

| | |
|----------------|-------------------------------|
| Item Type | Male Receptacle |
| Construction | Fabricated |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Material | Composite |
| UPC | 783585524207 |
| Color | Gray |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)