

Signal and Control, Linkosity, Male
Receptacle, 3-Wire, 10A 600V AC, PA Wire
Code, 1' Length

By Hubbell Wiring Device-Kellems
Catalog # [RM1004PM005](#)

Signal and Control, Linkosity, Male Receptacle, 3-Wire, 10A 600V
AC, PA Wire Code, 1' Length

Features

- Linkosity
- Male Receptacle
- 3-Wire
- 10A 600V AC

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#16 AWG

Current



Current / Amperage Rating	10 A
Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585131054
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)