

Linkosity, Male Receptacle 10A, 6P, 10'

By Hubbell Wiring Device-Kellems
Catalog # [RM1006PE010](#)

Linkosity, Male Receptacle 10A, 6P, 10'



Features

- Linkosity
- Male Receptacle 10A
- 6P
- 10'

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	6
Number Of Poles	6-Pole
Conductor Size	#16 AWG

Current

Current / Amperage Rating	10 A
Current Rating	10 A
Amperage Rating	10 A
Wattage	6000
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585524344
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)