

Signal and Control, Linkosity, Male Receptacle, 3-Wire, 10A 600V AC, PA Wire Code, 1' Length

By Hubbell Wiring Device-Kellems
Catalog # [RM1010PE005](#)

Signal and Control, Linkosity, Male Receptacle, 3-Wire, 10A 600V AC, PA Wire Code, 1' Length



Features

- Linkosity
- Male Receptacle
- 3-Wire
- 10A 600V AC

Application

Power and Control Integration

Specifications

| | |
|-------------------|----------|
| EU RoHS Indicator | Yes |
| Nema Rating | Non-NEMA |

Conductor

| | |
|----------------------|---------|
| Conductor Type | Copper |
| Number Of Conductors | 10 |
| Number Of Poles | 10-Pole |
| Conductor Size | #16 AWG |

Current

| | |
|---------------------------|-------------|
| Current / Amperage Rating | 7 A |
| Current Rating | 7 A |
| Amperage Rating | 7 A |
| Wattage | 4200 |
| Voltage Rating | 600V Max kV |

General

| | |
|----------------|-------------------------------|
| Item Type | Male Receptacle |
| Construction | Fabricated |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Material | Composite |
| UPC | 783585093055 |
| Color | Gray |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 25 |
|-----------------|----|

Product Assets

[Catalog \[English\]](#)