

Linkosity, 20A 5W, Male Receptacle, 1'

By Hubbell Wiring Device-Kellems
Catalog # [RM2005PB001](#)

Linkosity, 20A 5W, Male Receptacle, 1'



Features

- Linkosity
- 20A 5W
- Male Receptacle
- 1'

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	5
Number Of Poles	5-Pole
Conductor Size	#12 AWG

Current

Current / Amperage Rating	20 A
Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585409467
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)