

## Linkosity, Male Receptacle, 20A 5W

By Hubbell Wiring Device-Kellems  
Catalog # [RM2005PB010](#)

Linkosity, Male Receptacle, 20A 5W



### Features

- Linkosity20A 5W

### Application

Power and Control Integration

### Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

### Conductor

Conductor Type	Copper
Number Of Conductors	5
Number Of Poles	5-Pole
Conductor Size	#12 AWG

### Current

Current / Amperage Rating	20 A
---------------------------	------

Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

### General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585409481
Color	Gray

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)