

Linkosity Inlet, Hazardous Location, 20A 3-Wire

By Hubbell Wiring Device-Kellems
Catalog # [RM2703PB001](#)



Linkosity Inlet, Hazardous Location, 20A 3-Wire

Features

- Linkosity Inlet
- Hazardous Location
- 20A 3-Wire

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	3
Number Of Poles	3-Pole
Conductor Size	#12 AWG

Current

Current / Amperage Rating	20 A
Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585355825
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)