

Signal and Control, Linkosity, Male Receptacle, 4-Wire, 10A 600V AC, PB Wire Code, 1' Length

By Hubbell Wiring Device-Kellems
Catalog # [RM3004PB001S](#)

Signal and Control, Linkosity, Male Receptacle, 4-Wire, 10A 600V AC, PB Wire Code, 1' Length



Features

- Linkosity
- Male Receptacle
- 4-Wire
- 10A 600V AC

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	4
Number Of Poles	4-Pole
Conductor Size	#10 AWG

Current

Current / Amperage Rating	30 A
Current Rating	30 A
Amperage Rating	30 A
Wattage	18000
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite with Stainless Steel Body
UPC	783585243313
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)