

Linkosity, Hazardous Location, Inlet, 3-Wire, 20A, Super Neutral, Isolated Ground

By Hubbell Wiring Device-Kellems
Catalog # [RM7203PB001](#)

Linkosity, Hazardous Location, Inlet, 3- Wire, 20A, Super Neutral, Isolated Ground



Features

- Linkosity
- Hazardous Location
- Inlet
- 3- Wire
- 20A

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	3
Number Of Poles	3-Pole
Conductor Size	#12 AWG, #10 AWG Neutral

Current

Current / Amperage Rating	20 A
Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585355634
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[Spanish, French, English\]](#)