

Linkosity, Hazardous Location, Inlet, 5-Wire, 20A, Super Neutral, Isolated Ground

By Hubbell Wiring Device-Kellems
Catalog # [RM7205PB001](#)

Linkosity, Hazardous Location, Inlet, 5- Wire, 20A, Super Neutral, Isolated Ground



Features

- Linkosity
- Hazardous Location
- Inlet
- 5- Wire
- 20A

Application

Power and Control Integration

Specifications

EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Conductor Type	Copper
Number Of Conductors	5
Number Of Poles	5-Pole
Conductor Size	#12 AWG, #10 AWG Neutral

Current

Current / Amperage Rating	20 A
Current Rating	20 A
Amperage Rating	20 A
Wattage	12000
Voltage Rating	600V Max kV

General

Item Type	Male Receptacle
Construction	Fabricated
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Composite
UPC	783585355658
Color	Gray

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[Spanish, French, English\]](#)