

CLOCK HANG RECESS RCPT, 15A 125V, NI PL

By Hubbell Wiring Device-Kellems
Catalog # [RR151CHSS](#)

CLOCK HANG RECESS RCPT, 15A 125V, NI PL



Features

- 15A 125V
- NI PL

Application

Special Use Products

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Phase	Single Phase
Current / Amperage Rating	15 A

Connectivity	Back and Side Wired Screw Terminals
Current Rating	15 A
Amperage Rating	15 A
Wattage	1875
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Thermoplastic
UPC	883778100437
Color	Stainless Steel

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)