

## TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Single, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Light Almond

By Hubbell Wiring Device-Kellems  
Catalog # [RR155LA](#)

tradeSELECT® Straight Blade Receptacle Single 15A 6



### Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

### Application

Residential Receptacles

### Performance

Environmental - Operating temperature - -20°C to 60°C,  
Mechanical - Terminal - Terminal screws accepts up to #12 AWG,  
Push wire designed for #14 AWG solid copper wire only

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	6-15R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	250V kV

Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Side Wired
Wattage	3750
Voltage Rating	250V kV

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Light Almond
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
Specifications	<ul style="list-style-type: none"><li>• Material - Thermoplastic</li><li>• Number of Poles - 2 Pole</li><li>• Product Type - Receptacle</li><li>• Receptacle Type - Single</li></ul>
UPC	883778300585

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)