

RESI DUP RCPT 15A 125V 8 HOLE PUSH BR

By Hubbell Wiring Device-Kellems
Catalog # [RR15E](#)

RESI DUP RCPT 15A 125V 8 HOLE PUSH BR



Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

Specifications

| | |
|--------------------------|-------------------------------------------------|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator | Yes |
| Nema Rating | 5-15R |

Conductor

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire Grounding |
| Wire Size | #14 AWG to #12 AWG |
| Number Of Poles | 2-Pole |

Current

| | |
|-----------------|------|
| Current Rating | 15 A |
| Amperage Rating | 15 A |

| | |
|---------------------------|-----------------------|
| Phase | Single Phase |
| Current / Amperage Rating | 15 A |
| Connectivity | Eight Push Wire Holes |
| Wattage | 1875 |
| Voltage Rating | 125 VAC |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

General

| | |
|------------------------------|-------------------------------|
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Color | Brown |
| Item Type | Traditional Duplex |
| Material - Mounting Hardware | Screw Mounting |
| Material | Thermoplastic |
| UPC | 883778300882 |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog \[English\]](#)