



# TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Quick Wire Push Terminals, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Ivory

By Bryant  
Catalog # [RR15EQITR](#)



TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Quick Wire Push Terminals, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Ivory

## Features

- Smooth indented face appearance
- Tough thermoplastic ultrasonically welded cover and base
- Elongated strap with continuous plaster ears to secure device

## Application

Residential Receptacles

## Performance

Environmental - Operating temperature - -20°C to 60°C,  
Mechanical - Terminal - Terminal screws accepts up to #12 AWG,  
Push wire designed for #14 AWG solid copper wire only

## Specifications

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed E2186</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

## Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

## Current

Phase	Single Phase
Current / Amperage Rating	15 A

Connectivity	Eight Push Wire Holes
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 VAC
Wattage	1875
Voltage Rating	125 VAC

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## General

Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
Specifications	<ul style="list-style-type: none"> <li>• Base and Cover - Tough thermoplastic</li> <li>• Product Type - Receptacle</li> <li>• Receptacle Type - Duplex Quick Thread</li> <li>• Spring Material - Stainless Steel</li> </ul>
UPC	883778301384
Color	Ivory

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)