



TradeSelect, Straight Blade, Duplex
Receptacle, Tamper Resistant, Quick Wire
Push Terminals, 15A 125V, 2- Pole 3-Wire
Grounding, 5-15R, Brown

By Bryant
Catalog # [RR15EQTR](#)

TradeSelect, Straight Blade, Duplex Receptacle, Tamper
Resistant, Quick Wire Push Terminals, 15A 125V, 2- Pole 3-Wire
Grounding, 5-15R, Brown

Features

- Smooth indented face appearance
- Tough thermoplastic ultrasonically welded cover and base
- Elongated strap with continuous plaster ears to secure device

Application

Residential Receptacles

Performance

Environmental - Operating temperature - -20°C to 60°C,
Mechanical - Terminal - Terminal screws accepts up to #12 AWG,
Push wire designed for #14 AWG solid copper wire only

Specifications

Industry Standard(s)	• CSA Certified • UL Listed E2186
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Phase	Single Phase
Current / Amperage Rating	15 A



Connectivity	Eight Push Wire Holes
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 VAC
Wattage	1875
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
Specifications	• Base and Cover - Tough thermoplastic • Product Type - Receptacle • Receptacle Type - Duplex Quick Thread • Spring Material - Stainless Steel
UPC	883778301346
Color	Brown

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)