

Residential Wiring Devices, Straight Blade Devices, Duplex Receptacle, 8-Hole Push Wiring, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

By Hubbell Wiring Device-Kellems
Catalog # [RR15EW](#)

Residential Wiring Devices, Straight Blade Devices, Duplex Receptacle, 8-Hole Push Wiring, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White



Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A

Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Wattage	1875
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778300943

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)