



TradeSelect, Straight Blade, Duplex Receptacle, Cut Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

By Bryant
Catalog # RR15KI

TradeSelect, Straight Blade, Duplex Receptacle, Cut Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White



Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

Performance

Environmental - Operating temperature - -20°C to 60°C,
Mechanical - Terminal - Terminal screws accepts up to #12 AWG,
Push wire designed for #14 AWG solid copper wire only

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Phase	Single Phase
Current / Amperage Rating	15 A

Connectivity	Eight Push Wire Holes
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 VAC
Wattage	1875
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Material Specifications	Thermoplastic <ul style="list-style-type: none">• Material - Thermoplastic• Number of Poles - 2 Pole• Product Type - Receptacle• Receptacle Type - Duplex
UPC	883778100628
Color	Ivory

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)