

TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Cut Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

By Hubbell Wiring Device-Kellems
Catalog # [RR15KWTR](#)



TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, Cut Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

General

| | |
|------------------------------|--|
| Catalog Number | RR15KWTR |
| Color | White |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Traditional Duplex |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Specifications | <ul style="list-style-type: none">• Material - Thermoplastic• Number of Poles - 2 Pole• Product Type - Receptacle• Receptacle Type - Duplex |
| UPC | 883778301759 |

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

| | |
|----------------------------|-----------------------|
| Amperage Rating | 15 A |
| Connectivity | Eight Push Wire Holes |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 VAC |
| Wattage | 1875 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire Grounding |
| Wire Size | #14 AWG to #12 AWG |

Certifications And Compliance

| | |
|-------------|-------|
| Nema Rating | 5-15R |
|-------------|-------|

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 100 |
|-----------------|-----|

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RR15KWTR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2171_INSTALLINST](#)
[Sales Drawings - WDK_RR15KTR_DRAWING_PDF](#)
[Specifications - RR15KWTR Specification Sheet English](#)
[Specifications - RR15KWTR Specification Sheet French](#)