

TradeSelect, Straight Blade Devices, Tamper Resistant Residential Grade, Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Quick Plate, Brown

By Hubbell Wiring Device-Kellems
Catalog # [RR15QTR](#)

TradeSelect, Straight Blade Devices, Tamper Resistant Residential Grade, Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Quick Plate, Brown

Features

- Smooth indented face appearance
- Tough thermoplastic ultrasonically welded cover and base
- Elongated strap with continuous plaster ears to secure device

Application

Residential Receptacles

Performance

Environmental - Operating temperature - -20°C to 60°C,
Mechanical - Terminal - Terminal screws accepts up to #12 AWG,
Push wire designed for #14 AWG solid copper wire only

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed E2186
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A



Voltage Rating Description	125 VAC
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Push and Side Wire
Wattage	1875
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Brown
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
Specifications	<ul style="list-style-type: none">• Base and Cover - Tough thermoplastic• Product Type - Receptacle• Receptacle Type - Duplex Quick Thread• Spring Material - Stainless Steel
UPC	883778301551

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)