

## TradeSelect, Straight Blade, Duplex Receptacle, Weather and Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [RR15SALWRTR](#)

TradeSelect, Straight Blade, Duplex Receptacle, Weather and Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray



### Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

### Application

Residential Receptacles

### Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-15R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase

Current / Amperage Rating	15 A
Connectivity	Push and Side Wire
Wattage	1875
Voltage Rating	125 VAC

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Almond
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778303005

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)