

## TradeSelect, Straight Blade Residential Grade Receptacles, Tamper Resistant Single, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Self Grounding, Almond

By Hubbell Wiring Device-Kellems  
Catalog # [RR201ALTR](#)

TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Tamper Resistant Single, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Self Grounding, Almond



### Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

### Application

Residential Receptacles

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG
Number Of Poles	2-Pole

### Current

Current Rating	20 A
Amperage Rating	20 A

Voltage Rating Description	125 VAC
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Side Wired
Wattage	2500
Voltage Rating	125 VAC

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Almond
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778301940

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)