

## TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Almond

By Hubbell Wiring Device-Kellems  
Catalog # [RR201ALWRTR](#)

TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Almond

### Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

### Application

Residential Receptacles

### Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	No
Nema Rating	5-20R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG
Number Of Poles	2-Pole

### Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 VAC



Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Side Wired
Wattage	2500
Voltage Rating	125 VAC

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Almond
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778302923

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)