

## CLOCK HANG RECESS RCPT, 20A 125V, IV

By Hubbell Wiring Device-Kellems  
Catalog # [RR201CHI](#)

CLOCK HANG RECESS RCPT, 20A 125V, IV



### Features

- 20A 125V
- IV

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	20 A
Amperage Rating	20 A
Phase	Single Phase
Current / Amperage Rating	20 A

Connectivity	Back and Side Wired Screw Terminals
Wattage	2500
Voltage Rating	125 VAC

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Ivory
Item Type	Single Receptacle
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778100451

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)