



TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Tamper Resistant Single, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R

By Bryant
Catalog # [RR20I1TR](#)

tradeSELECT® Straight Blade TR Single 20A



Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

Performance

Environmental - Operating temperature - -20°C to 60°C,
Mechanical - Terminal - Terminal screws accepts up to #12 AWG,
Push wire designed for #14 AWG solid copper wire only

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A

Voltage Rating Description	125 VAC
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Side Wired
Wattage	2500
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Color	Ivory
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Material Specifications	Thermoplastic
	<ul style="list-style-type: none"> • Material - Thermoplastic • Number of Poles - 2 Pole • Product Type - Receptacle • Receptacle Type - Single
UPC	883778301988

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)