

## TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [RR2011WRTR](#)

TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory



### Features

- Tamper-resistant shutter and weather-resistance complies with national electrical code requirements
- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic cover and base

### Application

Residential Receptacles

### Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-1, Environmental - Operating temperature - -20°C to 60°C, without impact, Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA C22.2, No. 41

### Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA, C22.2, No. 41 File No. 23253</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2185</li> </ul>
Nema Rating	5-20R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG
Number Of Poles	2-Pole

### Current

Current Rating	20 A
----------------	------

Amperage Rating	20 A
Voltage Rating Description	125 VAC
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Side Wired
Wattage	2500
Voltage Rating	125 VAC

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Ivory
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
Specifications	<ul style="list-style-type: none"> <li>• Automatic Self-grounding Staple - Stainless Steel</li> <li>• Base - Thermoplastic</li> <li>• Contacts - Brass</li> <li>• Face - Thermoplastic</li> <li>• Mounting Screws - Zinc Plated Steel</li> <li>• Mounting Strap - Zinc Plated Steel</li> <li>• Terminal Screws - Brass</li> <li>• Termination Method - Side Wire Only</li> </ul>
UPC	883778302961

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)