

TradeSelect, Straight Blade, Single Receptacle, Weather Resistant, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Almond

By Hubbell Wiring Device-Kellems
Catalog # [RR205ALWR](#)

TradeSelect, Straight Blade, Single Receptacle, Weather Resistant, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Almond



Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	No
Nema Rating	6-20R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	250V kV

Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Side Wired
Wattage	5000
Voltage Rating	250V kV

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Almond
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778302763

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)