

TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black, With Plate

By Hubbell Wiring Device-Kellems
Catalog # [RR430WIPCN](#)



TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black, With Plate

Features

- Single Panel Mount Receptacle
- 30A 125/250V
- 3-Pole 4-Wire Grounding

Application

Residential Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	14-30R

Conductor

Number Of Wires	4-Wire Grounding
Wire Size	#10 AWG
Number Of Poles	3-Pole

Current

Current Rating	30 A
Amperage Rating	30 A
Phase	Single Phase

Current / Amperage Rating	30 A
Connectivity	Screw Terminals
Wattage	7500
Voltage Rating	125/250 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Flanged Single
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778301858

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)