



# TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

By Bryant  
Catalog # [RRD151](#)



TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

## Features

- Single Decorator
- Self Grounding
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

## Application

Residential Receptacles

## Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

## Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

## Current

Phase	Single Phase
Current / Amperage Rating	15 A

Connectivity	Side Wired
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 VAC
Wattage	1875
Voltage Rating	125 VAC

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## General

Item Type	Decorator Single
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Bryant
Material	Thermoplastic
UPC	883778100291
Color	Brown

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)