

TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Brown

By Hubbell Wiring Device-Kellems
Catalog # [RRD155](#)

TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Brown

Features

- Single Decorator Receptacle
- Self Grounding
- 15A 250V

Application

Residential Receptacles

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	6-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	250V kV



Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Side Wired
Wattage	3750
Voltage Rating	250V kV

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Brown
Item Type	Decorator Single
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778300660

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)