

## RESI DUP DEC RCPT 15A 125V 8 HOLE GY

By Hubbell Wiring Device-Kellems  
Catalog # [RRD15EGY](#)

RESI DUP DEC RCPT 15A 125V 8 HOLE GY



### Features

- Duplex Receptacle
- 15A 125V 8 HOLE GY

### Application

Residential Receptacles

### Specifications

|                          |   |
|--------------------------|---|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator        | Contact Manufacturer                            |
| Nema Rating              | 5-15R   |

### Conductor

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire Grounding   |
| Wire Size       | #14 AWG to #12 AWG |
| Number Of Poles | 2-Pole             |

### Current

|                           |              |
|---------------------------|--------------|
| Phase                     | Single Phase |
| Current / Amperage Rating | 15 A         |

|                 |                       |
|-----------------|-----------------------|
| Connectivity    | Eight Push Wire Holes |
| Current Rating  | 15 A                  |
| Amperage Rating | 15 A                  |
| Wattage         | 1875                  |
| Voltage Rating  | 125 VAC               |

### Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

### General

|                              |                               |
|------------------------------|-------------------------------|
| Item Type                    | Decorator Duplex              |
| Material - Mounting Hardware | Screw Mounting                |
| OEM Brand Name               | Hubbell Wiring Device-Kellems |
| Material                     | Thermoplastic                 |
| UPC                          | 883778300981                  |
| Color                        | Gray                          |

### Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

### Product Assets

[Catalog \[English\]](#)